

# SR Sanitary Electronic Pressure Transmitter

## Introduction

The Anderson-Negele SR series pressure transmitter offers not only a low profile design, but may be ordered with built-in LCD indication. The unit meets all sanitary requirements for finish and cleanability. It is designed and manufactured to withstand the harsh process and environmental conditions encountered in the food, dairy, and beverage industries.

Its one-piece stainless steel design incorporates a transducer and electronic circuitry to convert pressure and/or vacuum to a proportional 4-20 mA signal. The wide variety of fittings and ranges provide flexibility in specifying the best transmitter for any application. The unit is designed to operate at high process temperatures and withstand CIP/SIP conditions.

All units are supplied factory calibrated to standard, or custom ranges. For field maintenance, non-interactive zero, and span adjustments, as well as field accessible test points are provided. The optional LCD cap mounted display can be scaled to match actual process units, 0-100% of full scale, or 4-20 mA. This useful feature provides indication directly at the process, in addition to the standard 4-20 mA output.

Complete specifications and ordering information are available on the reverse. For more information please visit our Web Site at [www.anderson-negele.com](http://www.anderson-negele.com), or contact your local Authorized Anderson-Negele Distributor.

## Authorizations



## Features

- All-welded stainless steel construction
- Compact, low profile design
- Meets all FDA, USDA, and CGMP requirements
- 3-A compliant; Third party verified
- Product contact surface 316L stainless steel, optional Hasteloy "C" diaphragm
- Optional cap mounted LCD indicator



**Specifications**

Accuracy (includes repeatability, linearity, and hysteresis): ± 0.5% of span, full scale, for standard ranges except ranges below 0-50 psig ±1% full scale. All vacuum/pressure ranges and PSIA ranges are ±1%. High pressure (Homogenizer) fittings: ±.75%.  
 Repeatability: Better than 0.3% FSO  
 Hysteresis: Less than 0.2% FSO  
 Linearity (BFSL): ± 0.2% FSO  
 Stability: ± 0.3% of calibrated range/6 months  
 Over-Range Rating: 2 times base range, or 12,000 psig, whichever is less

Zero and Span Adjustments: ± 10% of range  
 Output: 4-20 mA DC  
 Excitation: 12-40 VDC (Absolute), 24 VDC Nominal regulated or unregulated. 17-45 VDC (Absolute) with display.

Loop Resistance: 0-600 ohms at 24 VDC  
 0-900 ohms at 30 VDC

Indication: Optional, 3-1/2 digit, .5" high LCD, cap mounted

Process Temperature Range: 20° to 300°F (-6.7 to 148.9°C)  
 (Horizontal mounting recommended for continuous operation over 275°F/135°C)

Process Temperature Effect: ±0.1 psig/5.5°C (10°F)  
 Response Time: 200 µSec  
 Ambient Temp. Operating Range: 0° to 120°F (-17.8° to 48.9°C)  
 Storage Temperature: -40° to 149°F (-40° to 65°C)  
 Mounting: Direct connection  
 Housing Material: 304 Stainless Steel  
 Housing Ratings: NEMA 4X, IP-66  
 Wetted Parts: 316L Stainless Steel standard; Hasteloy "C" diaphragm optional (Std. for homogenizer fittings)

Surface Finish (wetable parts): Ra max = 25 microinches (.6 microns)  
 Recommended Cable: 18-24 AWG, foil shielded, and PVC coated. (3/16 - 1/4 OD insulation)  
 Wiring Connection: Screw Terminal; Accessible via removable screw cap conduit housing  
 Standards: Designed and manufactured to sound engineering practices in accordance with Article 3.3 of the PED 97/23/EC

**Order Information**



RANGE (Available Units)	
025	30/0 (M)
028	30/0/15 (C)
029	30/0/30 (C)
031	30/0/60 (C)
032	30/0/100 (C)
066	0/30 (G,A)
068	0/50 (G,A,B)
069	0/60 (G)
070	0/99 (G)
071	0/100 (G,A)
073	0/150 (G,A)
074	0/160 (G,A)
075	0/200 (G,A)
077	0/300 (G,A)
081	0/500 (G)
084	0/,1000 (G)
086	0/2,000 <sup>1</sup> (G)
088	0/3,000 <sup>1</sup> (G)
090	0/5,000 <sup>1</sup> (G)
093	0/10,000 <sup>1</sup> (G)
094	0/15,000 <sup>3</sup> (G)
095	0/20,000 <sup>3</sup> (G)
251	-1/0/1 (B)
286	-1/0/2.5 (B)
217	-1/0/3 (B)
056	-1/0/4 (B)
304	-1/0/7 (B)
057	0-2 (B)
235	0-3 (B)
192	0-4 (B)
060	0-6 (B)
061	0-10 (B)
065	0-20 (B)

**ENGINEERING UNITS**

G	PSIG
M	Hg (inches Mercury)
A	PSIA
B	BAR
C	Vacuum/Pressure ("Hg & PSIG)

**FITTING**

004	1-1/2" Tri-Clamp®
005	2" Tri-Clamp®
010	1-1/2" APC "K"
011	2" APC "K"
016	1-1/2" Cherry "I" (male)
017	2" Cherry "I" (male)
027	1-1/2" G & H "H" line (male)
028	2" G & H "H" Line (male)
044	1-1/2" #14 Bevel Seat (w/nut)
045	2" #14 Bevel Seat (w/nut)
056	High Pressure (Homogenizer) w/out Flange
057	High Pressure (Homogenizer) with 7/8" Flange
058	High Pressure (Homogenizer) with 1-1/8" Flange
059	1-1/2" NPT <sup>4</sup>
117	High Pressure (Rannie) <sup>4</sup>
129	38mm IDF w/Nut <sup>4</sup>
131	51mm IDF w/Nut <sup>4</sup>
157	High Pressure (Niro) <sup>4</sup>

CABLE LENGTH	
00	No Cable
05	25'
10	50'
20	100'
24	200'
A0	Quick Disconnect Receptacle (QDR)
A1	QDR & Field Wireable Connector (FWC)
A2	QDR w/25 ft Molded Cordset
A3	QDR w/50 ft Molded Cordset
A5	QDR w/100 ft Molded Cordset
A9	QDR w/200 ft Cable

  

DIAPHRAGM FINISH	
1	Standard (R <sub>s</sub> 25)

  

DIAPHRAGM MATERIAL	
1	316L Stainless
2	Hastelloy "C" (Standard for fittings 056, 057, 058, 117, 157)

  

DISPLAY VALUE	
0	None
G	PSIG <sup>2</sup>
A	PSIA
B	BAR
R	mA (milliamphere, for vac/press.)
Q	% (percent, for vac/press.)

<sup>1</sup> Available with High Pressure Fittings Only (056-058; 117,157).  
<sup>2</sup> If over 1,000 PSIG, units are PSIG X 10.  
<sup>3</sup> Available with High Pressure Fitting 157 Only  
<sup>4</sup> Not 3-A compliant

