



## Sanitary tank cleaner fits through 50mm (2") opening

### Alfa Laval GJ A2

#### Application

Designed to fit through a 2" (5.08 cm) sanitary fitting, the Alfa Laval GJ A2 is part of the world-renowned Gamajet range of high impact tank cleaning devices. It is the perfect alternative to time-intensive spray balls and costly manual cleaning. Made of FDA compliant materials, this device is flow-through in design, meaning it requires no grease or oil in the gears. Compact and efficient, the Alfa Laval GJ A2 allows for space saving while maintaining the impact, durability, and range required for optimal rotary impingement tank cleaning in sanitary environments.

#### Working principle

The Gamajet range of high impact tank cleaning devices combine pressure and flow to create high impact cleaning jets. Cleaning occurs at the point at which the concentrated stream impacts the surface. It is this impact and the tangential force that radiates from that point which blasts contaminants from the surface, scouring the tank interior. In conjunction with this impact, the device is engineered to rotate in a precise, repeatable and reliable, 360° pattern. This full-coverage, global indexing pattern ensures the entire tank interior is cleaned, every time.




#### TECHNICAL DATA

Lubricant . . . . . Self-lubricating  
Max. throw length . . . . . 4 - 5 m (12 - 14 ft.)


#### Pressure

Working pressure . . . . . 2.75 - 14 bar (40 - 200 PSI)  
Recommended pressure . . . . . 4 - 10 bar (50 - 150 PSI)

#### Cleaning Pattern



First Cycle



Full Pattern

The above drawings show the cleaning pattern achieved on a cylindrical horizontal vessel. The difference between the first cycle and the full pattern represents the number of additional cycles available to increase the density of the cleaning.

#### Certificate

2.1 material certificate

#### PHYSICAL DATA

##### Materials

316L, PPS, PTFE, FKM (EPDM and FFKM available).

##### Temperature

Max. working temperature . . . . . 95°C (203°F)  
Max. ambient temperature . . . . . 140°C (284°F)

##### Weight

. . . . . 2.26 kg (5 lbs.)

##### Surface finish

. . . . . 0.8 µm (32 Ra)

##### Connections

Standard thread . . . . . 1.5" Tri-Clover,  
Available option . . . . . ¾" NPT, 1" Tri-Clover, 1½"  
TUBE

##### Options

Electronic rotation sensor to verify 3D coverage.


##### Caution

Do not use for gas evacuation or air dispersion.




Disclaimer: Information in this product data leaflet is intended for general guidance purposes. Specific data for device selection and sizing is available upon request.

### Flow Rate (2 nozzle)




### Impact Throw Length




- - - Wetting, — Impact


### Flow Rate (4 nozzle)




### Impact Throw Length (4 nozzle)



## Dimensions



## Cleaning Time



	A	B	C	D	E	F	G	H
mm	503	343	431	31	30	47	47	61
in	19.8	13.5	18.1	1.2	1.2	1.9	1.9	2.4

## Standard Design


The choice of nozzle diameters can optimize jet impact length and flow rate at the desired pressure. As standard documentation, the Alfa Laval GJ A2 can be supplied with a "Declaration of Conformity" for material specifications.

## TRAX simulation tool


TRAX is a unique software that simulates how the Alfa Laval GJ A2 performs in a specific tank or vessel. The simulation gives information on wetting intensity, pattern mesh width and cleaning jet velocity. This information is used to determine the best location of the tank cleaning device and the correct combination of flow, time, and pressure to implement.

A TRAX demo containing different cleaning simulations covering a variety of applications can be used as a reference and documentation for tank cleaning applications. The TRAX demo is free and available upon request.


## Wetting Intensity



TD 523-208



D2.2m(85"), H3.6m(140"), 2x3.81mm (2xØ3/16") Time = 2 min.



D2.2m(85"), H3.6m(140"), 2x3.81mm (2xØ3/16") Time = 8 min.

Alfa Laval reserves the right to change specifications without prior notification. ALFA LAVAL is a trademark registered and owned by Alfa Laval Corporate AB.

ESE02996EN 1015

© Alfa Laval

---

**How to contact Alfa Laval**

Contact details for all countries are continually updated on our website. Please visit [www.alfalaval.com](http://www.alfalaval.com) to access the information direct.